

REA PC Scan


BAR CODE VERIFIER

Check printed symbols or films

The REA PC-Scan incorporates a software package and a measuring device (Laser Device). The Laser Device has a built in measuring unit with a solid state red light laser driven by a motor. Measurements are transferred to the software for evaluation. The evaluation is divided into two parts. One part according to ISO/IEC 15416 (CEN or ANSI evaluation) the other part according to Symbology specifications and/or standards. In case of EAN Codes ISO/IEC 15420 (traditional evaluation)

Software Controlled

Against the standards and specifications measured values are presented clearly on the screen.



The screen shows the two evaluation methods at the same time. ISO/IEC 15416 method evaluates in detail the reflectance profile with different aspects. Quality is presented in 5 steps. The user is able to preset a quality requirement according to the application or material characteristics. The traditional evaluation gives detailed metric results, bar width and positions as extreme and average values direct on the screen. Detail values for each bar and space can be shown in a separate table. As well as printed codes the REA PC-Scan is able to measure positive and negative Film Masters according to ISO/IEC 15421.



Powerful, precise verification

- Contactless verification by a precision measuring unit
- Meets new ISO/IEC standard 15416 and incorporates traditional method
- Meets ISO/IEC standard 15421 for Film Master measurement
- 155mm wide measuring path and optional 240mm
- Clear presentation of results on PC screen
- Automatic size determination and metric values in microns
- Automatic calibration for each measurement

REA PC Scan Options & Specifications

Options

Optional Codes

This software has optional extra symbologies. The measuring program is also included in this package. Unknown Codes or random samples can be measured by the measuring program. This is useful for color contrast evaluation in preprint or to evaluate unreadable bar codes.

Bar Code Symbologies:

EAN-13, UPC-A, EAN-8, UPC-E, including Instore and 2- or 5-digit Add-Ons, Code 128, EAN 128, 2/5 interleaved, ITF-14, Code 39, PZN-Code (Pharma-Zentral-Nummer), Code 32 (Italian Pharmacode)

Film platen

The Film platen has a 1 cm slit instead of the 3 cm slit in the standard platen. A positive and negative Film Master is included for calibration purposes.

Optional Codes:

EAN-D3, Code 128 UPU, 2/5 Frachtpost, 2/5 5 bars (straight), 2/5 3 bars (Matrix), 2/5 IATA, Codabar ANSI, CODABAR Monarch, Code 39 Full ASCII, Code 39 UPU, Code 93, MSI, Pharma and Mini Pharma Code, 2/5 Siemens, 2/5 Hoeft&Wessel, Measuring program for unknown Codes

Adaptor for curved surfaces

This option is a special bottom plate prism. This supports the measurement of bar codes on circular bodies like cans, bottles and beakers. A defined position is required for measuring. Bar code have to be printed in ladder form on curved surfaces.

Technical Specifications

- PC with Windows (95, 98, NT, 2000, XP) required for Operation, one serial port
- Size of Laser Device: 251x84x92 mm (WxDxH), standard version 155 mm measuring width
- Size of Laser Device: 222x84x92 mm (WxDxT) optional version with 240 mm measuring width for wide codes
- Light source solid state laser with 670 nm wave length or optional 635 nm (both red light)
- Laser class II
- Selectable aperture 4, 6 and 8 mil
- Accuracy +/- 2 µm metrical +/-5% contrast
- Power supply 100 Volt to 240 Volt
- Convertible primary socket adapter (EURO, US, UK); others on request

Models

The measuring unit of the REA PC-Scan (Laser Device) is available in four different models. Two different red light wave lengths either 670 or 635 nm and two different measuring widths either 155 mm or 240 mm.

Features

- Evaluation according to Symbology standards and specifications (traditional evaluation)
- Evaluation according to ISO/IEC 15416 (CEN/ANSI evaluation)
- Selection of quality grades (CEN/ISO or ANSI)
- Preset of required quality grade in comparison to the measured grade
- Average measurement
- PCS evaluation at two different positions
- Evaluation of bar and space reflectance values in addition to contrast values
- Manufactured in conformity to ISO/IEC 15426-1
- Automatic reflectance calibration and internal metric built in scale
- Autodiscrimination of Symbologies
- Static contrast measurement
- Verification of light margins
- Verification of Ratio (relation between thin and thick bars)
- Automatic size verification
- Check digit verification
- Verification of EAN-128 data structure
- Zoomable scan reflectance profile for additional manual evaluation
- Indication of defects, edge contrast and symbol contrast in scan reflectance profile
- Measuring of free selectable reflectance values and distances within the scan reflectance profile
- Contactless measurement
- Linear measurement for maximum accuracy
- Supported languages German, English, French and Spanish
- Export of measured data in CSV table
- Report print on PC default printer
- Important functions can be operated directly from the Laser Device
- Shipment in a case with all required accessories (without PC).

Specifications are subject to change without notice

Contact Details

Isis Integration Ltd
7c Ladycross Business Park
Hollow Lane, Dormansland
LINGFIELD
RH7 6PB

Tel: 01342 871010
Email: info@isisintegration.co.uk
Web: www.isisintegration.co.uk